


TECHSPEC® 12.5mm Dia., Uncoated, 30' Wedge, Fused Silica Wedged Window



TECHSPEC® Fused Silica Wedged Windows

Stock **#34-241** 3-5 DAYS

- 1 + **S\$166.75**

ADD TO CART

Qty 1-5

S\$166.75

Qty 6+

S\$133.40

Volume Pricing

[Request Quote](#)

Get Product Downloads



Clear Aperture CA (mm):
11.25

Diameter (mm):
12.50 +0.0/-0.10

Thickness (mm):
3.00 ±0.20

Coating: Uncoated
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 0.52 (+5 to +35°C) 0.57 (0 to +200°C) 0.48 (-100 to +200°C)
Edges: Fine Ground
Index of Refraction n_d: 1.458
Substrate: ☐ Fused Silica (Corning 7980)
Surface Flatness (P-V): λ/10
Surface Quality: 20-10
Type: Wedged Window
Wavelength Range (nm): 200 - 2200
Young's Modulus (GPa): 73
Wedge Angle: 30' ±10'

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant