

TECHSPEC® 125mm, Side Drive, Standard Top, English Extended Micrometer



125mm Micrometer Drive Stage

Stock #66-455 3-5 DAYS

⊖ 1 ⊕

S\$1,013.55

ADD TO CART

Qty 1-2
S\$1,013.55
Qty 3+
S\$887.11
Volume Pricing
Request Quote

Get Product Downloads

Type of Movement:
Linear (X)

Guide System:
Crossed Roller Bearing

Type of Drive:
English Micrometer

Drive Orientation:

Side Drive
Type: English
Stage Size (mm): 125 x 125
Travel (inches): 2
Center Hole: ¼-20
Construction: Aluminium Stage
Leadscrew Pitch (mm): 0.635
Load Capacity (kg): 20
Mounting Threads: (21) ¼-20, (8) 2-56, (4) 6-32
Stage Size (inches): 4.92 x 4.92
Straight Line Accuracy (µm): 2
Pitch (arcsec): 40
Yaw (arcsec): 30

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 233: Contains SVHC(s)
