

TECHSPEC[®] 12.7mm - 12.7mm (Rotatable), Right Angle Post Clamp



#58-994

Stock **#58-994** [CONTACT US](#)

-

1

+

S\$48⁻¹⁶

ADD TO CART

Volume Pricing	
Qty 1-9	S\$48.16 each
Qty 10+	S\$46.44 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Universal	Type:
Rotatable	Function:

Physical & Mechanical Properties

12.7 - 12.7 Post Clamp Size (mm):

Regulatory Compliance

Compliant RoHS 2015:

Compliant Reach 224:

View Certificate of Conformance:

PRODUCT DETAILS

- Basic Building Block for Optical Systems
 - Fixed Options for Mounting 12.7mm to 12.7mm or 12.7mm to 12.0mm Posts Available
 - Rotatable Option for 12.7mm to 12.7mm Posts
 - Aluminum Mount Construction
- TECHSPEC® Right Angle Post Clamps are basic building blocks for optical systems. This post clamp is used to mount two of our 0.5" stainless steel posts at 90° from each other. The posts are locked in place with two ¼-20 thumbscrews. The heavy-duty design provides a stable, secure fit for tightly spaced systems. TECHSPEC Right Angle Post Clamps are constructed of anodized aluminum. Fixed clamp, fixed clamp kit, or rotatable clamp options are available.

TECHNICAL INFORMATION

