

127mm Clear Aperture, 2 Arcsec, Aluminum Retroreflector



Stock **#49-671** CLEARANCE 3-5 DAYS

-

1

+

S\$10,034.00

ADD TO CART

Qty 1+
S\$10,034.00

Volume Pricing
Request Quote

Get Product Downloads

Beam Deviation (arcsec):
2.00

Clear Aperture CA (mm):
127.0

Coating:
Enhanced Aluminum (450-650nm)

Diameter (mm):
166.70

Exiting Wavefront Accuracy:
1.2λ

Substrate:  BOROFLOAT®

Surface Quality:
80-50

Mounting Threads:
(7) ¼-20, (6) M6 x 1.0

Type:
Retroreflector

Dimensional Tolerance (mm):
±1.6

Image Orientation:
Left-Handed

Ray Deviation (°):
180

Wavelength Range (nm):
400 - 700

Regulatory Compliance

RoHS 2015:
[Compliant](#)

REACH 201:
[Compliant](#)

Certificate of Conformance:
[View](#)