

[See all 4 Products in Family](#)

12mm Dia. x 48mm FL, Commercial Grade, Plano-Convex Lens



Stock #23-074 CLEARANCE **15 In Stock**

[Other Coating Options](#)

1 **\$28^{.70}**

ADD TO CART

Volume Pricing	
Qty 1+	\$28.70 each
Need More?	Request Quote

Product Downloads

General

Plano-Convex Lens **Type:**

Physical & Mechanical Properties

12.00 +0.00/-0.10 **Diameter (mm):**

6.00 **Centering (arcmin):**

2.00 **Center Thickness CT (mm):**

1.26 Edge Thickness ET (mm):

≥10.2 Clear Aperture CA (mm):

Optical Properties

48.00 Effective Focal Length EFL (mm):

46.69 Back Focal Length BFL (mm):

Uncoated Coating:

N-BK7 Substrate:

±1 Focal Length Tolerance (%):

24.81 Radius R₁ (mm):

4.00 f#:

0.13 Numerical Aperture NA:

Regulatory Compliance

View Certificate of Conformance:

Product Details

- Feature Standard Designs and Specifications
- Also Available with [MgF₂ Coating](#)
- For More Options, View [Precision Quality Plano-Convex \(PCX\) Lenses](#)

Plano convex lenses (PCX) have one flat and one outward curving face and a positive focal length. They are ideal for collecting and focusing light in imaging applications. They are also useful in a variety of applications involving emitters, detectors, lasers, and fiber optics. Commercial Grade Uncoated Plano-Convex (PCX) Lenses offer commercial quality, at an affordable price.

Technical Information

