

12" x 11.5" 0°, Glossy, 3M Light Control Film



Stock **#52-385** **5 In Stock**

-

1

+

S\$250⁶⁰

ADD TO CART

Volume Pricing	
Qty 1+	S\$250.60 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Specialty Window

Type:

Physical & Mechanical Properties

304.80

Length (mm):

12 x 11.5	Dimensions (inches):
304.8 x 292.1	Dimensions (mm):
0.021	Thickness (inches):
0.50	Thickness (mm):
292.10	Width (mm):
Optical Properties	
Polycarbonate	Substrate: ☐
Environmental & Durability Factors	
-40 to +120	Operating Temperature (°C):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 240:

PRODUCT DETAILS

- Ideal for PrivacyViewing
- Contrast Enhancement and Improved Sunlight Readability
- Reduces Unwanted Reflections

3MLight Control Film is a high-performance plastic, containing closely spaced microlouvers. These louvers simulate a tiny venetian blind, blocking out unwanted ambient light and controlling the direction of display light. The results of these features are higher contrast enhancement, improved readability in sunlight, and the ability to direct light, as well as restricting readability to a single viewer for privacy.

TECHNICAL INFORMATION



