

13mm Travel, Metric Micrometer, Solid-Top Ball Bearing Stage



2.62" Center drive stage and its X-Y configuration

Stock **#37-977** 3-5 DAYS

− 1 +

S\$825.05

ADD TO CART

Qty 1+

S\$825.05

Volume Pricing

[Request Quote](#)

[Get Product Downloads](#)

Type of Movement: Linear (X)
Guide System: Ball Bearing
Type of Drive: Metric Micrometer
Drive Orientation: Center Drive
Type: English
Stage Size (mm): 66.5 x 66.5
Travel (mm): 13
Construction: Aluminium Stage
Graduation (mm): 0.01
Height (inches): 1.00
Height (mm): 25.4
Load Capacity, Normal (lbs): 62
Note: Solid Top
Stage Size (inches): 2.62 x 2.62
Straight Line Accuracy (inches): 0.00008/inch of travel
Weight (lbs): 0.72
Thrust Capacity, T_a (lbs): 10
Thrust Capacity, T_b (lbs): 2

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View