

14mm Dia. x -21mm FL, Negative Meniscus Lens, Grade 2



Stock #96-202 CLEARANCE 20+ In Stock

-

1

+

S\$7^{.35}

ADD TO CART

Volume Pricing	
Qty 1+	S\$7.35 each
Need More?	Request Quote

Product Downloads

Physical & Mechanical Properties	
14.00	Diameter (mm):
Optical Properties	
-21.00	Effective Focal Length EFL (mm):
1.5	f/#:
0.33	Numerical Aperture NA:

Material Properties

Grade 2	Grade:
---------	--------

Regulatory Compliance

View	Certificate of Conformance:
----------------------	-----------------------------

Product Details

- Ideal for Experimenting and Prototyping Applications
- Quantities Extremely Limited, Buy While Supplies Last
- For Even More Deals, Check out [Mega Clearance: Optics](#)

Experimental Quality Negative Meniscus Lenses are offered in several experimental grade options. Grade 1 is standard optical glass, edged, free of visible scratches, chips, stains, or oxidation. Grade 2 is unedged, non-optical glass, small chips, slight stains, or other defects. They may have slight edge cement separation.

Note: Specifications for experimental grade optics may vary as much as 10% from those listed. Also, no additional information is available other than what is provided.

Technical Information

