

TECHSPEC[®] 14mm Uncoated, Amici Roof Prism



Amici Roof Prisms

Stock #45-261 3-5 DAYS

-

1

+

S\$140.65

ADD TO CART

Qty 1-5

S\$140.65

Qty 6+

S\$110.20

Volume Pricing

[Request Quote](#)

Get Product Downloads



Clear Aperture CA (mm):
13.00

Coating:
Uncoated

Substrate: ☐
[N-BK7](#)

Surface Quality: 60-40
Type: Amici Roof Prism
Dimensional Tolerance (mm): +0/-0.1
Angle Tolerance (arcmin): ±5
Resolution (arcsec): 6.00
Bevel: Protective bevel as needed
Image Orientation: Right-Handed
Ray Deviation (°): 90
Wavelength Range (nm): 350 - 2200
Surface Flatness (P-V): λ/2

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View