

1.5" LED Spot Light, 520nm

See More by [Advanced Illumination](#)



Stock **#66-817** [CONTACT US](#)

- 1 + **S\$622.05**

ADD TO CART

Qty 1+

S\$622.05

Volume Pricing

[Request Quote](#)

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Color:
Green

Diameter (mm):
38.00

Model Number:
SL2420-520100L-24

Length (mm):
54.00

Operating Temperature (°C): 0 to 65
Wavelength (nm): 520.00
Working Distance (mm): 100.00
Intensity Control Option: No
LED Lifetime (hours): 50,000
Wavelength Tolerance (nm): ±25
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-773 China: #66-855
Light Distribution (%): ±10 Edge to Edge (Dependent on Working Distance)
Number of LEDs: 20.00
Number of Channels: 1.00
Field Coverage (mm): 43.00
Type of Illumination: LED Illuminator
Manufacturer: Advanced Illumination
Geometry: Spot Light
Illumination Mode: Constant

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant