

1.5" LED Spot Light, 880nm, Strobed

See More by [Advanced Illumination](#)



Stock #83-276 [CONTACT US](#)

-

1

+

S\$1,006.30

ADD TO CART

Qty 1+
S\$1,006.30

Volume Pricing
Request Quote

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Color:
Infrared

Diameter (mm):
38.00

Model Number:
SL2420-660-ISU

Length (mm):
54.00

Operating Temperature (°C): 0 to 65
Wavelength (nm): 880.00
Working Distance (mm): 100.00
Intensity Control Option: No
LED Lifetime (hours): 50,000
Wavelength Tolerance (nm): ±25
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-773 China: #66-855
Light Distribution (%): ±10 Edge to Edge (Dependent on Working Distance)
Number of LEDs: 20.00
Number of Channels: 1.00
Field Coverage (mm): 43.00
Type of Illumination: LED Illuminator
Note: Requires a 24V power supply #66-855 . European power supply #35-200 also available.
Manufacturer: Advanced Illumination
Geometry: Spot Light
Illumination Mode: Strobed

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View