

[See all 2 Products in Family](#)

150W EKE, Replacement Bulb

See More by [Dolan-Jenner](#)



115V, DC950H Illuminator, #62-002



Stock **#39-606** **16 In Stock**

- 1 + **\$42.⁰⁰**

ADD TO CART

Volume Pricing	
Qty 1-9	\$42.00 each
Qty 10-24	\$35.00 each
Need More?	Request Quote

Product Downloads

General

Lamp Lifetime (hours):
200

Type of Illumination:
Accessory

Environmental & Durability Factors

3200.00

Color Temperature (K):

Regulatory Compliance

[View](#)

Certificate of Conformance:

Product Details

- DC-Regulated Power Supply Less Than 0.5%
- Low Output Power Ripple Less Than 0.4%
- Remote Intensity Control from 0-5VDC Analog
- 200 to 10,000 Hours Lamp Life

The DC-950H is a cost effective 150W quartz halogen light source designed specifically for machine vision lighting. This light source has a compact footprint, making it a great addition to any lab or workspace. In addition to the 0 to 100% intensity control and heat absorbing filter, the basic model features less than 0.4% variation in the power output as compared to typical 2% variance in non-regulated or AC-regulated illuminators. Built-in remote interface permits precise intensity control of output power via 0-5VDC analog input or an 8 bit digital interface. Dolan-Jenner SX Fiber Optic [Adapters](#) are sold separately and required for use with a light guide.

Technical Information

