

[See all 2 Products in Family](#)

# 150W EKE, Replacement Bulb

See More by [Dolan-Jenner](#)



115V, DC950H Illuminator, #62-002



Stock **#39-606** 17 In Stock

-

1

+

S\$42<sup>.00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-9        | S\$42.00 each                 |
| Qty 10-24      | S\$35.00 each                 |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

| General                            |           |
|------------------------------------|-----------|
| Lamp Lifetime (hours):             | 200       |
| Type of Illumination:              | Accessory |
| Environmental & Durability Factors |           |

3200.00

Color Temperature (K):

Regulatory Compliance

View

Certificate of Conformance:

## Product Details

- DC-Regulated Power Supply Less Than 0.5%
- Low Output Power Ripple Less Than 0.4%
- Remote Intensity Control from 0-5VDC Analog
- 200 to 10,000 Hours Lamp Life

The DC-950H is a cost effective 150W quartz halogen light source designed specifically for machine vision lighting. This light source has a compact footprint, making it a great addition to any lab or workspace. In addition to the 0 to 100% intensity control and heat absorbing filter, the basic model features less than 0.4% variation in the power output as compared to typical 2% variance in non-regulated or AC-regulated illuminators. Built-in remote interface permits precise intensity control of output power via 0-5VDC analog input or an 8 bit digital interface. Dolan-Jenner SX Fiber Optic **Adapters** are sold separately and required for use with a light guide.

## Technical Information

