

[See all 9 Products in Family](#)

## 15mm Dia x 60mm Focal Length, Spherical Mirror



Stock **#46-236** **2 In Stock**

- 1 + S\$70<sup>.70</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-49	<b>S\$70.70</b> each
Qty 50-99	<b>S\$63.00</b> each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

Spherical Mirror **Type:**

#### Physical & Mechanical Properties

15.00 +0.00/-0.30 **Diameter (mm):**

Ground **Back Surface:**

3.00 **Center Thickness CT (mm):**

±0.30	<b>Center Thickness Tolerance (mm):</b>
3.23	<b>Edge Thickness ET (mm):</b>
Ground	<b>Edges:</b>
120.0	<b>Radius R (mm):</b>
<b>Optical Properties</b>	
Metal	<b>Coating Type:</b>
Protected Aluminum (400-2000nm)	<b>Coating:</b>
400 - 2000	<b>Wavelength Range (nm):</b>
60.00	<b>Effective Focal Length EFL (mm):</b>
<a href="#">N-BK7</a>	<b>Substrate:</b> <input type="checkbox"/>
f/4	<b>Aperture (f/#):</b>
R <sub>avg</sub> >85% @ 400 - 700nm R <sub>avg</sub> >90% @ 400 - 2000nm	<b>Coating Specification:</b>
±2	<b>Focal Length Tolerance (%):</b>
λ/4	<b>Surface Accuracy:</b>
60-40	<b>Surface Quality:</b>
120.00	<b>Radius of Curvature (mm):</b>

<b>Regulatory Compliance</b>	
<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Compliant</a>	<b>Reach 247:</b>

## Product Details

- Aluminum Coating
  - Ideal for UV, Visible, and IR Applications
  - Multiple Diameter and f# Combinations Available
- N/4 Spherical Mirrors have flat rear surfaces and aluminum coated spherical front surfaces. These mirrors are ideal for applications in UV, VIS, and IR wavelength ranges.

## Technical Information

