

TECHSPEC[®] 15mm, Uncoated, N-SF11 Micro Right Angle Prism



N-SF11 Right Angle Prisms

Stock #45-950 3-5 DAYS

-

1

+

S\$232.00

ADD TO CART

Qty 1-5

S\$232.00

Qty 6+

S\$208.80

Volume Pricing

[Request Quote](#)

Get Product Downloads



Coating:

Uncoated

Substrate: ☐

[N-SF11](#)

Surface Quality:

20-10

Type: Right Angle Prism
Dimensional Tolerance (mm): +0/-0.1
Angle Tolerance (arcmin): ±2
Bevel: Protective bevel as needed
Length of Hypotenuse (mm): 21.20
Length of Legs (mm): 15.00
Image Orientation: Left-Handed
Ray Deviation (°): 90
Wavelength Range (nm): 400 - 2500
Surface Flatness (P-V): λ/4

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View