

1.5" Width, Dovetail Carrier



1.5" Width, Dovetail Carrier, #55-339

Stock **#55-339** 20+ In Stock

-

1

+

S\$129⁵⁰

ADD TO CART

Volume Pricing	
Qty 1-4	S\$129.50 each
Qty 5+	S\$123.62 each
Need More?	Request Quote

Product Downloads

General	
English	Type:
Carrier	Note:
Physical & Mechanical Properties	
Linear (X)	Type of Movement:
	Guide System:

Dovetail	
1.5	Length (inches):
	Length (mm):
38.10	
Construction:	
Black Anodized Aluminum	

Hardware & Interface Connectivity

Type of Drive:	
Manual	

Threading & Mounting

Mounting Threads:	
(6) ¼-20 on 1"	


Regulatory Compliance

RoHS 2015:	
Compliant	
Certificate of Conformance:	
View	
REACH 241:	
Compliant	

Product Details

- Wide Range of Carrier Length and Mounting Hole Options Available
 - Low Profile Design with Smooth Movement
 - Increased Stability and <1mrad Straight Line Accuracy
- Dovetail Optical Rail Systems are designed for easy and stable installation and positioning of various optical components along the same axis. The rails feature slotted holes that allow them to be fixed to standard ¼-20 TPI and M6 breadboards or optical tables. Carriers are available with different lengths and hole patterns to meet various mounting needs including options that are directly compatible with our [TECHSPEC® Manual Stages](#) for precision alignment. Carriers utilize a unique two-piece design to prevent the locking screws from contacting the rail and to allow easy attachment and removal. All Dovetail Optical Rail System parts are constructed of black anodized aluminum to minimize stray reflections or glare.
- Note:** Rails and carriers are sold separately.

Technical Information



Stock No.	L	A	B	C	D	# Slots	# C'bores
#54-401	12	6	4	—	—	3	—
#54-402	36	18	16	4	6	5	2

Dovetail Optical Rail

Top view dimensions: A, B, C, D, 1.50, 2.30, 1.70, 0.40, 2.30, 1.70, 0.25, 0.75, 1.25, 0.25, 3.00.

Labels: C'bore for 1/4 S.H.C.S., Slots for 1/4 S.H.C.S., L.

Units: inches

