

## TECHSPEC® 16 x 23mm Protected Gold, λ/4 Mirror



Stock #32-432 3-5 DAYS

⊖ 1 ⊕ **S\$101.50**

**ADD TO CART**

Qty 1-5

**S\$101.50**

Qty 6+

**S\$81.20**

Volume Pricing

[Request Quote](#)

Get Product Downloads



Surface Flatness (P-V):  
λ/4

Substrate:   
[BOROFLOAT®](#)

Back Surface:  
Ground

**Surface Quality:**

60-40

**Dimensions (mm):**

16.0 x 23.0

**Dimensional Tolerance (mm):**

+0/-0.5

**Coating Specification:**R<sub>avg</sub> >96% @ 700 - 2000nmR<sub>avg</sub> >96% @ 2000 - 10,000nm**Coating:**

Protected Gold (700-10000nm)

**Coating Type:**

Metal

**Bevel:**

Protective bevel as needed

**Clear Aperture (%):**

85

**Edges:**

Fine Ground

**Thickness (mm):**

5.00 +0.5/-0

**Type:**

Flat Mirror

**Wavelength Range (µm):**

0.7 - 10

**Wavelength Range (nm):**

700 - 10000

**Length (mm):**

23.00

**Width (mm):**

16.00

**Damage Threshold, Reference:** 0.8 J/cm<sup>2</sup> @ 1064nm, 10ns

## Regulatory Compliance

**RoHS 2015:**[Compliant](#)**Certificate of Conformance:**[View](#)**Reach 235:**[Compliant](#)