

**TECHSPEC® 16.25" Diameter x 80" FL Uncoated, Parabolic Mirror**



Stock #32-725-000 3-5 DAYS

⊖ 1 ⊕ **S\$10,139.85**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-2                       |
| S\$10,139.85                  |
| Qty 3+                        |
| S\$8,618.80                   |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads

Substrate: [BOROFLOAT®](#) [SUPREMAX®](#)

Focal Length Tolerance (%):  
±1.5

Surface Quality:  
60-40

Surface Accuracy:  
λ/8

|                                                     |
|-----------------------------------------------------|
| <b>Diameter (inches):</b><br>16.25 +0.06/-0         |
| <b>Diameter (mm):</b><br>412.80 +1.5/-0             |
| <b>Effective Focal Length EFL (inches):</b><br>80.0 |
| <b>Effective Focal Length EFL (mm):</b><br>2,032.00 |
| <b>Radius of Curvature (mm):</b><br>4,064.00        |
| <b>Aperture (f/#):</b><br>f/4.9                     |
| <b>Coating:</b><br>Uncoated                         |
| <b>Coating Type:</b><br>Uncoated                    |
| <b>Back Surface:</b><br>Ground                      |
| <b>Clear Aperture CA (mm):</b><br>372               |
| <b>Edge Thickness ET (inches):</b><br>3.25          |
| <b>Edge Thickness ET (mm):</b><br>82.60             |
| <b>Type:</b><br>Parabolic Mirror                    |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |