

17.9mm Dia x 73.4mm FL, Grade 1, Plano-Convex Lens



Stock **#77-585** CLEARANCE CONTACT US

-

1

+

S\$14^{.43}

ADD TO CART

Volume Pricing	
Qty 1+	S\$14.43 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General	
	Type: Plano-Convex Lens
Physical & Mechanical Properties	
17.90	Diameter (mm):

Optical Properties	
73.40	Effective Focal Length EFL (mm):
4.1	f/#:
0.12	Numerical Aperture NA:
Regulatory Compliance	
View	Certificate of Conformance:

PRODUCT DETAILS

- Ideal for Experimenting and Prototyping Applications
 - Quantities Extremely Limited, Buy While Supplies Last
 - For Even More Deals, Check out [Mega Clearance: Optics](#)
- Plano-convex (PCX) lenses have one flat and one outward curved face. They have a positive focal length, making them ideal for collecting and focusing light in imaging applications.

1 - 24.9mm Experimental Quality Plano-Convex (PCX) Lenses are offered in several experimental grade options. Grade 1 is standard optical glass, edged, free of visible scratches, chips, stains, or oxidation. Grade 2 is unedged, non-optical glass, small chips, slight stains, or other defects. They may have slight edge cement separation.

Note: Specifications for experimental grade optics may vary as much as 10% from those listed. Also, no additional information is available other than what is provided.

TECHNICAL INFORMATION

