

1/8" x 36" Dual Branch Light Guide



Stock #54-199 3-5 DAYS

-

1

+

S\$297.25

ADD TO CART

Qty 1+

S\$297.25

Volume Pricing

[Request Quote](#)

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Acceptance Angle (°):
68.00

Minimum Bend Radius (mm):
19.05

Fiber Bundle Diameter (inches):
0.125/0.089 (Ø1/Ø2)

Length (inches):
36.00

Numerical Aperture NA: 0.55
Operating Temperature (°C): -40 to +107
Fiber Diameter (µm): 50.00
Length Tolerance (inches): ± 0.5
Packing Fraction (%): 82.00
Index of Refraction n_d - Core: 1.581
Index of Refraction n_d - Cladding: 1.487
Transmission Loss: 6% per foot at 600nm
Type of Illumination: Fiber Optic Light Guide
Compatible Light Guide Adapter: SX: #38-943 MX: #66-904
Wavelength Range (nm): 400 - 2000
Geometry: Spot Light

Regulatory Compliance

Reach 174: Compliant
RoHS: Not Compliant
Certificate of Conformance: View