

[See all 12 Products in Family](#)

# 19" x 47", English Lab Table

See More by [TMC](#)



Stock **#54-253** [CONTACT US](#)

-

1

+

**S\$2,240<sup>.00</sup>**

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | <b>S\$2,240.00</b> each       |
| Need More?     | <a href="#">Request Quote</a> |

| Product Downloads |
|-------------------|
|-------------------|

## SPECIFICATIONS

### General

English      **Type:**

### Physical & Mechanical Properties

**Thickness (mm):**

|                                                                                                                                               |                       |
|-----------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|
| 50.00                                                                                                                                         |                       |
| 47.0                                                                                                                                          | Length (inches):      |
| 19.0                                                                                                                                          | Width (inches):       |
| Construction:<br>Stainless Steel (400 Series) Top and Bottom<br>Plates, Plated Steel Honeycomb Core, High<br>Pressure Laminate Core Sidewalls |                       |
| ≤3                                                                                                                                            | Core Cell Area (cm²): |
| 0.13                                                                                                                                          | Flatness (mm):        |
| 62.0                                                                                                                                          | Weight (lbs):         |

### Threading & Mounting

Mounting Threads:  
(765) ¼-20 Tapped on 1" Centerlines, on 1.5"  
Corners

### Regulatory Compliance

RoHS 2015:  
[Compliant](#)

Certificate of Conformance:  
[View](#)

## PRODUCT DETAILS

- Stainless Steel
- Economically Priced
- Lightweight Design

TMC™ CleanTop® Optical Honeycomb Breadboards are ultra-light (9 lbs/ft2, 44kg/m2) breadboards that employ countersunk, tapped holes in a thin top-skin of stainless steel. Top and bottom plates have a matte finish to lower reflectance and are ferromagnetic for mounting with magnetic bases. The tapped mounting holes allow for mounting with our English or Metric posts and post holders, as well as most commonly used optical mounts. TMC™ CleanTop® Optical Honeycomb Breadboards feature holes that are on 1" (25mm) centers with 1.5" (37.5mm) corners. Individually sealed holes allow for easy cleaning of spills

**Note:** Due to size and weight, shipping method and charges will differ from standard catalog charges; please contact our [Sales Department](#) for detailed information. Also note that these items will not be shipped overnight.