

[See all 5 Products in Family](#)

19mm Dia x 476mm FL, Grade 1, Plano-Convex Lens



Stock #76-173 CLEARANCE **16 In Stock**

- 1 + **\$14^{.35}**

ADD TO CART

Volume Pricing	
Qty 1+	\$14.35 each
Need More?	Request Quote

Product Downloads

General

Plano-Convex Lens **Type:**

Physical & Mechanical Properties

19.00 **Diameter (mm):**

Optical Properties

476.00 **Effective Focal Length EFL (mm):**

Coating:

25.05 **f#:**
0.02 **Numerical Aperture NA:**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Product Details

- Ideal for Experimenting and Prototyping Applications
- Quantities Extremely Limited, Buy While Supplies Last
- For Even More Deals, Check out [Mega Clearance: Optics](#)

Plano-convex (PCX) lenses have one flat and one outward curved face. They have a positive focal length, making them ideal for collecting and focusing light in imaging applications.

1 - 24.9mm Experimental Quality Plano-Convex (PCX) Lenses are offered in several experimental grade options. Grade 1 is standard optical glass, edged, free of visible scratches, chips, stains, or oxidation. Grade 2 is unedged, non-optical glass, small chips, slight stains, or other defects. They may have slight edge cement separation.

Note: Specifications for experimental grade optics may vary as much as 10% from those listed. Also, no additional information is available other than what is provided.

Technical Information

