

1" Travel, Eng Micrometer, Thru-Hole 5.00" Stage



Stock #38-204 3-5 DAYS

⊖ 1 ⊕

S\$1,773.35

ADD TO CART

Qty 1+
S\$1,773.35

Volume Pricing
Request Quote

Get Product Downloads

Type of Movement:
Linear (X)

Guide System:
Ball Bearing

Type of Drive:
Digital Micrometer (English)

Drive Orientation:
Center Drive

Type:
English

Stage Size (mm): 127 x 127
Travel (inches): 1
Construction: Aluminum Top and Base/440C Stainless Steel Bearings
Graduation (inches): 0.00005
Load Capacity, Normal (lbs): 105
Load Capacity, T_a (lbs): 30
Load Capacity, T_b (lbs): 2
Note: Thru-Hole
Stage Size (inches): 5.00 x 5.00
Straight Line Accuracy (inches): 0.00008 per inch of travel
Weight (lbs): 3.1

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View