

2" Fiber Optic Diffuse Axial Illuminators



2" Fiber Optic Diffuse Axial Illuminators (#53-380)

Stock **#53-380** 3-5 DAYS

⊖ 1 ⊕

\$S\$1,276.00

ADD TO CART

Qty 1+

\$S\$1,276.00

Volume Pricing

[Request Quote](#)

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Numerical Aperture NA:
0.55 nominal

Fiber Diameter (µm):
50 (0.002" nominal)

Construction:
Black Anodized Aluminum

Packing Fraction (%):
83% nominal

Transmission Loss:
10% per ft. at 660nm

Type of Illumination:
Fiber Optic Light Guide

Geometry:
Diffuse Axial

Regulatory Compliance

Reach 174:
[Compliant](#)

RoHS:
Not Compliant

Certificate of Conformance:
[View](#)
