

2.00", English Rotary Stage



Stock #33-465 **2 In Stock**

-

1

+

SS\$1,589^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	SS\$1,589.00 each
Need More?	Request Quote

Product Downloads

General

English	Type:
---------	-------

Physical & Mechanical Properties

1	Weight (lbs):
44.4 x44.4	Stage Size (mm):
1.75 x1.75	Stage Size (inches):
	Construction:

Aluminum top and base; steel tangent arm drive	
0.25" Dia. Thru	Center Hole:
±5 (Fine), 360 (Coarse)	Travel (°):
12	Increments (arcmin):
10	Load Capacity, Normal (lbs):
4	Load Capacity, Vertical (lbs):
Rotary	Type of Movement:
Ball Bearing	Guide System:
2	Table Diameter (inches):

Hardware & Interface Connectivity

Type of Drive:	
Tangent Arm	

Threading & Mounting

Mounting Threads:	
(12) 6-32 on 0.625", 1.125" & 1.50" dia. B.C.	

Regulatory Compliance

RoHS 2015:	
Compliant	
Certificate of Conformance:	
View	

Product Details

- Low Wear, Low Friction Movement with Coarse or Fine Adjustment
 - 2 or 2.62" Diameter Stages with Tapped Mounting Holes
 - Calibrated Dial with 12 Minute Vernier for Accurate Read-Out
- Compact miniature stages provide low-friction rotary movement with both coarse and fine adjustment. This allows for quick rotation over a continuous 360° travel, plus precise angular adjustment at any selected position. Features include preloaded angular contact ball bearing system, a positive position lock, a 2.00" or 2.62" diameter stage with tapped mounting holes and a calibrated dial with six minute vernier for accurate positional read-out. It can be combined with our compatible linear translation stages for multi-axis linear-rotary applications.

Technical Information

