

[See all 11 Products in Family](#)

2" Travel, 0.001" Grad., 0.5" Stem Dia. Mic. Drive F-Face



Drive Mechanisms

Stock **#33-737** [CONTACT US](#)

-

1

+

S\$323⁴⁰

ADD TO CART

Volume Pricing	
Qty 1-9	S\$323.40 each
Qty 10-24	S\$291.06 each
Need More?	Request Quote

Product Downloads

General

English	Type:
Mitutoyo	Manufacturer:

Physical & Mechanical Properties

2	Travel (inches):
	Graduation (inches):

0.001	
12	Stem Diameter (mm):
Plain/Flat	Stem/Spindle:
29	Stem Length (mm):
8	Spindle Diameter (mm):
34	Min. Spindle Length (mm):
21	Max. Diameter (mm):
119.5	Overall Length (mm):

Hardware & Interface Connectivity

English Micrometer	Type of Drive:
--------------------	----------------

Regulatory Compliance

Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	REACH 241:

Product Details

- Micrometer, Fine Screw, Digital and Differential Options Available
 - Compatible with our [Ball Bearing Stages](#)
- These drive mechanisms add versatility to our selection of [ball bearing stages](#). Four options are available: micrometer (English and Metric), fine screw, digital, and differential.
- Please reference individual product descriptions to see which stages are compatible with each drive mechanism.

Technical Information

