

## 200 lp/mm, 1" x 3", FS w/ Fluorescent, Ronchi



Stock #57-882 CLEARANCE **1 In Stock**

S\$910<sup>00</sup>

ADD TO CART

#### Volume Pricing

Qty 1-4	<b>S\$910.00</b> each
Qty 5+	<b>S\$864.78</b> each
Need More?	<a href="#">Request Quote</a>

#### Product Downloads

#### Physical & Mechanical Properties

3.00	Length (inches):
12.7 x 25.4	Pattern Size (mm):
1.10	Thickness (mm):
1.00	Width (inches):

#### Optical Properties

---

**Coating:**  
Vacuum Deposited Chrome  
Fluorescent Peak Excitation @ 365 nm; Fluorescent  
Peak Emission @ 550 nm

**Frequency (lp/mm):**  
200.00

---

**Substrate:**   
[Fused Silica](#) with Fluorescent Backing

**Optical Density OD (Average):**  
3.00

---

## Regulatory Compliance

**RoHS 2015:**  
[Compliant](#)

**Certificate of Conformance:**  
[View](#)

---

**Reach 240:**  
[Compliant](#)

## Product Details

- Used for Evaluation of Resolution, Field Distortion, and Parfocal Stability
- Ideal for Reticle and Field Calibration Requirements
- Available on Float Glass, Fused Silica, Fused Silica with Fluorescent Backing, and [Opal](#).

Precision Ronchi Ruling Glass slides are excellent for evaluating resolution, field distortion, and parfocal stability, especially of microscopes. Many different Linepairs Per Millimeter (lp/mm) versions available.

---

;