

203 x 254mm Sandblasted Glass



Stock #02-147 **20+ In Stock**

- 1 + \$81^{.20}

ADD TO CART

Volume Pricing	
Qty 1-10	\$81.20 each
Qty 11+	\$64.05 each
Need More?	Request Quote

Product Downloads

General

Ground Glass Diffuser **Type:**

Physical & Mechanical Properties

203.00 x 254.00 **Dimensions (mm):**

1.60 **Thickness (mm):**

203.00 **Width (mm):**

254.00

Length (mm):

Optical Properties

Float Glass

Substrate:

350 - 2000

Wavelength Range (nm):

Regulatory Compliance

[Compliant](#)

RoHS 2015:

[View](#)

Certificate of Conformance:

[Compliant](#)

Reach 247:

Product Details

- Large Sizes Available
- 120-Grit Sandblast
- Economically Priced

Commercial Quality Sandblasted Glass is finely etched on one side to allow improved light diffusion. With a 120-grit sandblast spray, it is ideal for use in rear projection screen systems.