

[See all 44 Products in Family](#)

20mm Diameter 120 Grit Ground Glass Diffuser



Stock **#83-380** 20+ In Stock

-

1

+

S\$33^{.60}

ADD TO CART

Volume Pricing	
Qty 1-10	S\$33.60 each
Qty 11+	S\$29.75 each
Need More?	Request Quote

Product Downloads

General	
Ground Glass Diffuser	Type:
Sandblasted on first surface	Note:
Physical & Mechanical Properties	
20.00 ±0.25	Diameter (mm):
Ground	Edges:

Grit:	
120	
Thickness (mm):	
1.60	

Optical Properties

Coating:	
Uncoated	
Substrate:	
Float Glass	

Wavelength Range (nm):	
350 - 2000	

Regulatory Compliance

RoHS 2015:	
Compliant	
Certificate of Conformance:	
View	

Reach 247:	
Compliant	


Product Details

- Available in Sizes Ranging from 5mm Diameter to 250mm Square
- Low Scatter Loss
- Evenly Ground Surface for Even Diffusion
- [Fused Silica Substrates](#) Available

Ground Glass Diffusers are comprised of high tolerance, quality ground glass making them ideal for a variety of industrial applications. The float glass substrate has excellent visible transmission and is ideal for general diffusing applications. A 120-grit, 220-grit or 600-grit (as noted) sandblast is used to create a diffuse surface on the glass. Ground Glass Diffusers have even diffusion across the entire surface from undergoing two orthogonal passes during this sandblast process. The scattering is a compromise of low scatter loss and medium diffusion. Typical applications include use in screens, illuminator diffusion, and targets.

Can't find what you need? Get a quick [custom quote](#).

Technical Information



Quote Your Size

Compatible Mounts