

TECHSPEC® 20mm Enhanced Aluminum Coated, N-BK7 Right Angle Mirror



Stock #45-594

CONTACT US

-

1

+

S\$152.25

ADD TO CART

Qty 1-5
S\$152.25
Qty 6+
S\$121.80
Volume Pricing
Request Quote

Get Product Downloads



Surface Flatness (P-V):

λ/8

Substrate:

[N-BK7](#)

Surface Quality:

40-20

Length of Legs (mm):

20.00
Dimensional Tolerance (mm): ±0.1
Coating Specification: R _{avg} >95% @ 450 - 650nm
Coating: Enhanced Aluminum (450-650nm)
Coating Type: Metal
Angle Tolerance (arcmin): ±2
Bevel: Protective bevel as needed
Clear Aperture CA (mm): 25.45 x 18.00
Length of Hypotenuse (mm): 28.30
Type: Right Angle Mirror
Wavelength Range (µm): 0.45 - 0.65
Wavelength Range (nm): 450 - 650
Damage Threshold, Reference: ☐ 0.2 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View