

TECHSPEC® 20mm, Uncoated, N-BK7 High Tolerance RA Prism



N-BK7 High Tolerance Right Angle Prisms

Stock **#32-547** 3-5 DAYS

⊖ 1 ⊕

S\$142.10

ADD TO CART

Qty 1-5

S\$142.10

Qty 6+

S\$113.83

Volume Pricing

[Request Quote](#)

Get Product Downloads

Angle Tolerance (arcsec):
±15

Coating:
Uncoated

Substrate: ☐
[N-BK7](#)

Surface Quality:

40-20
Type: Right Angle Prism
Dimensional Tolerance (mm): +0/-0.1
Bevel: Protective bevel as needed
Length of Hypotenuse (mm): 28.30
Length of Legs (mm): 20.00
Image Orientation: Left-Handed
Ray Deviation (°): 90
Wavelength Range (nm): 350 - 2200
Surface Flatness (P-V): $\lambda/8$

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View