See all 1 Products in Family

20" x 24" UV Filter Sheet

Stock **#39-426** **20+ In Stock**

- 1 + **S$41**.30

ADD TO CART

Volume Pricing	
Qty 1+	**S$41.30** each
Need More?	Request Quote

Product Downloads

General

Type:

Longpass Filter

Physical & Mechanical Properties

Dimensions (mm):

508.0 x 609.6

Length (mm):

609.60

Dimensions (inches):

20 x 24

Width (mm):

508.00

Optical Properties

Cut-On Wavelength (nm):
400.00

Substrate:
Polyester Film

Color:
Clear

Wavelength Range (nm):
200 - 750

Regulatory Compliance

Reach 191:
Compliant

RoHS 2015:
Compliant

Certificate of Conformance:
View

Product Details

- Virtually Transparent, Flexible Polyester Filter
- Deep-Dyed PET Substrate to Absorb UVA, UVB, and UVC Rays
- <10% Transmission Below 390nm

Flexible Thin Film UV Filters block UVA, UVB, and UVC wavelengths while transmitting visible illumination. These filters are ideal for applications where ultraviolet rays have harmful effects.

Technical Information



;