

23" Dual Branch Semi-Rigid Light Guide



Stock **#54-212** 3-5 DAYS

- 1 +

S\$611.90

ADD TO CART

Qty 1+
S\$611.90

Volume Pricing
Request Quote

Get Product Downloads

Acceptance Angle (°): 68.00
Minimum Bend Radius (mm): 101.6
Fiber Bundle Diameter (inches): 0.265
Length (inches): 23.00
Numerical Aperture NA: 0.55

Operating Temperature (°C): -40 to +107
Fiber Diameter (µm): 50.00
Type: Dual Branch
Length Tolerance (inches): ±0.5
Packing Fraction (%): 82.00
Index of Refraction n_d - Core: 1.581
Index of Refraction n_d - Cladding: 1.487
Transmission Loss: 6% per foot at 600nm
Type of Illumination: Fiber Optic Light Guide
Compatible Light Guide Adapter: SX: #38-947
Geometry: Spot Light

Regulatory Compliance

Reach 174: Compliant
RoHS: Not Compliant
Certificate of Conformance: View
