

240mm Length, Fixed Laser Holder



#54-990, #54-991

Stock **#54-991** 20+ In Stock

⊖ 1 ⊕ \$317⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	\$317.80 each
Qty 5-25	\$280.84 each
Qty 26-49	\$258.72 each
Need More?	Request Quote

Product Downloads

General

Fixed **Type:**

Cylindrical Tube **Type of Optics:**

Physical & Mechanical Properties

240.00 **Length (mm):**

660

Weight (g):

Black Anodized Aluminum
Construction:

Twin Ring Mount Adjustment Screw Pitch (mm):
0.5

Threading & Mounting

Size of Compatible Optics (mm):
20.0 - 55.0

Compatible Post:
M6 x 1.0

Regulatory Compliance

RoHS 2015:
[Exempt](#)

Certificate of Conformance:
[View](#)

Reach 247:
[Contains SVHC\(s\)](#)

Product Details

- Twin Ring Mount Design
- Fixed and Adjustable Versions
- Ideal for He-Ne Lasers

• [Posts](#) and [Post Holders](#) Required for Mounting

Designed for [Helium-Neon Lasers](#), this mount is ideal for any optical tube assembly. [Posts](#) and [Post Holders](#) are required for mounting to a breadboard.

Mounting hole is M6 x 1.0

Technical Information

