

See More by [CCS](#)



☐ - 1 ☐ + **S\$784^{.00}**

Volume Pricing	
Qty 1+	\$S784.00 each
Need More?	Request Quote

General

Intensity Control Option:
256 steps

256 steps

Number of Channels:

3

Type of Illumination:

Power Supply

Note:

Compatible to all High Angle, Low Angle and Diffuse Ring Lights, as well as up to 100 x 100mm Backlights and R75 Dome Lights.

Strobe Lighting Time Range:	
40μs - 40ms (10 steps)	
Physical & Mechanical Properties	
84 W x 120 H x 83 D	Dimensions (mm):
	Weight (kg):
0.6	
Electrical	
Power Consumption (W):	
78	
Regulatory Compliance	
Certificate of Conformance:	
View	

Product Details