

2.5 OD, 25.4mm Dia., Reflective Neutral Density Filter



Stock #27-932 CLEARANCE 3-5 DAYS

- 1 +

S\$21.68

ADD TO CART

Qty 1+
S\$21.68

Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
25.40 ±0.3

Optical Density OD (Average):
2.5

Substrate: ☐
Borosilicate

Coating:
Metallic Based ND

Thickness (mm):
1.00

Thickness Tolerance (mm):	±0.25
Transmission (%):	0.3
Type:	Neutral Density Filter
Parallelism (arcmin):	±3
Dimensional Tolerance (mm):	±0.3
Clear Aperture (%):	>90
Optical Density Tolerance (%):	±10

Regulatory Compliance

RoHS:	Compliant
Certificate of Conformance:	View