

25 x 25mm Left-Handed Circular Polarizing Film (CP42HE)



Stock **#88-083** CLEARANCE 3-5 DAYS

- 1 +

S\$16.43

ADD TO CART

Qty 1+
S\$16.43

Volume Pricing
Request Quote

Get Product Downloads

Substrate: [Polymer Film CP42HE](#)

Length (mm):
25.00

Operating Temperature (°C):
-40 to +80

Dimensions (mm):
25.0 x 25.0

Thickness (mm):
0.27 ±0.04

Transmission (%) : 42.00
Type : Left-Handed Circular Polarizer
Dimensional Tolerance (mm) : +0.0/-0.3
Construction : Polarizing Film
Wavelength Range (nm) : 400 - 700
Polarization Efficiency (%) : >99.90
Heat Resistance (°C x Hours) : 80 x 500
Width (mm) : 25.00
#Sorting : 10.00

Regulatory Compliance

RoHS 2015 : Compliant
Certificate of Conformance : View
Reach 235 : Contains SVHC(s)