

25 x 38mm, 75R/25T, Plate Beamsplitter



Stock #31-435 3-5 DAYS

- 1 +

S\$79.75

ADD TO CART

Qty 1-9

S\$79.75

Qty 10+

S\$60.90

Volume Pricing

[Request Quote](#)

Get Product Downloads



Coating Specification:

Surface 1: Dielectric, ±5% R/T @ 550nm
Surface 2: Uncoated

Construction:

Plate

Dimensional Tolerance (mm):

±0.38

Dimensions (mm): 25.0 x 38.0
Edges: Cut
Reflection/Transmission Ratio (R/T): 75/25
Substrate: Float Glass
Surface Flatness (P-V): 4 - 6λ
Surface Quality: 80-50
Thickness (mm): 3.00
Type: Standard Beamsplitter
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant