

TECHSPEC® 25/25.4mm Diameter, C-Mount Thick Optic Mount



Stock #56-354 **20+ In Stock**

⊖ 1 ⊕ S\$138⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	S\$138.60 each
Qty 5-9	S\$123.06 each
Qty 10-25	S\$113.68 each
Need More?	Request Quote

Product Downloads

General

Fixed **Type:**

Optic Mount (Fixed) **Function:**

Circular **Type of Optics:**

Physical & Mechanical Properties

24.2 **Extension Length (mm):**

28.2 **Total Length (mm):**

3.3 **Min. Thickness of Compatible Optics (mm):**

11.5 **Max. Thickness of Compatible Optics (mm):**

22.00 **Clear Aperture CA (mm):**

Construction:
Black Anodized Aluminum (6061 T6)

30.0 **Outer Diameter (mm):**

Threading & Mounting

C-Mount **Thread Type:**

25.0 - 25.4 **Diameter of Compatible Optics (mm):**

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 250:
[Compliant](#)

Product Details

25/25.4mm holder is a 3 part assembly and adds 24.2mm to the system length.

- Mounts for Simple Lenses, Achromats, Filters, or Reticles
- Designed to Integrate with Any C, S, or T-Mount Components
- Optic is Held in Place with Included Retaining Ring

TECHSPEC® C, S, and T-Mount Circular Optic Mounts are designed to mount a variety of circular optical components into C, S, or T-Mount compatible systems. An included threaded retainer ring, designed to accept a standard spanner wrench, securely holds the optical component. These circular optic mounts are compatible with a wide variety of Edmund Optics optomechanical components utilizing C, S, or T-Mount threads, such as [extension tubes](#) and [kinematic mounts](#). TECHSPEC® C, S, and T-Mount Circular Optic Mounts are threaded for 1" x 32TPI, M12 x 0.5, or M42 x 0.75 mounting, with 30mm, 16mm, and 48mm outer diameters, respectively. These mounts are ideal for creating and personalization of a diverse range of optical systems.

Note: [#56-353](#), [#56-354](#), [#52-933](#), and [#52-292](#) are all 3-part assemblies

Technical Information

