

254 x 313mm, 4-6λ Mirror



4-6λ First Surface Mirrors

Stock **#32-248** 3-5 DAYS

⊖ 1 ⊕

S\$221.85

ADD TO CART

Qty 1-5

S\$221.85

Qty 6+

S\$177.63

Volume Pricing

[Request Quote](#)

Get Product Downloads

Surface Flatness (P-V):

4 - 6λ

Substrate: ☐

Float Glass

Surface Quality:

80-50

Dimensions (mm):

254.0 x 313.0 ±0.76
Coating Specification: R _{avg} >85% @ 400 - 700nm
Coating: Protected Aluminum (400-700nm)
Coating Type: Metal
Angle of Incidence (°): 45.00
Bevel: Protective as needed
Clear Aperture (%): >90
Thickness (mm): 6.00
Type: Flat Mirror
Wavelength Range (nm): 400 - 700
Length (mm): 313.00
Width (mm): 254.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant