

25.4mm Dia. Left-Handed Plastic Circular Polarizer (CP42HE)



Stock #88-098

3-5 DAYS

-

1

+

S\$47.85

ADD TO CART

Qty 1-5
S\$47.85
Qty 6+
S\$40.60
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
25.40

Substrate:

CP42HE on PMMA

Operating Temperature (°C):
-40 to +80

Thickness (mm):
2.29 ±0.24

Transmission (%) : 42.00
Type : Left-Handed Circular Polarizer
Dimensional Tolerance (mm) : +0.0/-0.3
Construction : Polarizing Film on PMMA
Wavelength Range (nm) : 400 - 700
Polarization Efficiency (%) : >99.90
Heat Resistance (°C x Hours) : 80 x 500
#Sorting : 4.00

Regulatory Compliance

RoHS 2015 : Compliant
Certificate of Conformance : View
Reach 235 : Compliant