

TECHSPEC® 25.4mm Dia. x 2mm Thickness 3-5µm Coated Silicon Window



TECHSPEC Silicon (Si) Windows

Stock **#20-037** 3-5 DAYS

-

1

+

S\$297.25

ADD TO CART

Qty 1-10

S\$297.25

Qty 11+

S\$267.52

Volume Pricing

[Request Quote](#)

Get Product Downloads



Bevel:
Protective as needed

Clear Aperture (%):
90.00

Clear Aperture CA (mm):
22.86

Diameter (mm): 25.40 +0.0/-0.1
Thickness (mm): 2.00 ±0.1
Coating: BBAR (3000-5000nm)
Coating Specification: R _{avg} <3.0% @ 3 - 5µm
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 2.55
Density (g/cm³): 2.33
Edges: Fine Ground
Index of Refraction n_d: 3.422 @ 5µm
Knoop Hardness (kg/mm²): 1150
Parallelism (arcmin): <3
Poisson's Ratio: 0.265
Substrate: Silicon (Si)
Surface Flatness (P-V): 1λ
Surface Quality: 60-40
Type: Protective Window
Wavelength Range (nm): 3000 - 5000
Young's Modulus (GPa): 140

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant