

25.4mm Travel, Metric Micrometer, Solid Top 127.0mm Stage



Stock #55-463 [CONTACT US](#)

- 1 + **S\$1,773.35**

ADD TO CART

Qty 1+
S\$1,773.35

Volume Pricing
Request Quote

Get Product Downloads

Type of Movement:
Linear (X)

Guide System:
Ball Bearing

Type of Drive:
Digital Micrometer (Metric)

Drive Orientation:
Center Drive

Type:
Metric

Stage Size (mm): 127 x 127
Travel (mm): 25
Construction: Aluminum Top and Base/440C Stainless Steel Bearings
Graduation (mm): 0.001
Load Capacity, Normal (kg): 48
Load Capacity, T_a (kg): 13.6
Load Capacity, T_b (kg): 0.9
Note: Solid Top
Stage Size (inches): 5.00 x 5.00
Straight Line Accuracy (µm): 2 per 25 mm of travel
Weight (g): 1400

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View