

25° Diffusing Angle 12.5mm Unmounted



Stock #35-866

CLEARANCE

3-5 DAYS

-

1

+

S\$130.50

ADD TO CART

Qty 1-5

S\$130.50

Qty 6+

S\$97.88

Volume Pricing

[Request Quote](#)

Get Product Downloads

Angle Tolerance (°):

±2.5

Diffusing Angle (°):

25 (FWHM)

Diameter (mm):

12.50

Dimensional Tolerance (mm):

±0.5

Operating Temperature (°C): -30 to +100 (Maximum of 240 Hours)
Substrate: ☐ Polycarbonate
Thickness (mm): 0.78
Transmission (%): >85
Type: Holographic Diffuser
Wavelength Range (nm): 400 - 700
Construction: Unmounted
Damage Threshold, By Design: ☐ 0.22 J/cm ² @ 1064nm, 10ns (typical)

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant