

TECHSPEC® 25mm Dia., UV Enhanced Aluminum, $\lambda/10$ Stemmed Mirror



TECHSPEC® Stemmed Mirror



Stock #14-580 CLEARANCE 3-5 DAYS

- 1 +

S\$191.40

ADD TO CART

Qty 1-5

S\$191.40

Qty 6+

S\$152.25

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.00 +0.00/-0.10

Surface Flatness (P-V):
 $\lambda/10$

Substrate: Fused Silica (Corning 7980)
Back Surface: Commercial Polish
Surface Quality: 20-10
Coating Specification: R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm
Coating: Enhanced Aluminum (250-700nm)
Coating Type: Metal
Clear Aperture (%): 90.00
Edges: Ground, protective bevel as needed
Thickness (mm): 13.00 ±0.20
Type: Stemmed Mirror
Wavelength Range (nm): 250 - 700
Compatible Kinematic Mount: #58-853
Stem Diameter (mm): 12.50 +0.00/-0.10
Stem Length (mm): 6.50 ±0.20

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View