

[See all 7 Products in Family](#)

25mm Dia. x 200mm FL Uncoated, DCX N-K5 Lens



Stock **#32-902** CLEARANCE **20+ In Stock**

- 1 + **\$33^{.25}**

ADD TO CART

Volume Pricing	
Qty 1+	\$33.25 each
Need More?	Request Quote

Product Downloads

General

	Type:
Double-Convex Lens	

Physical & Mechanical Properties


25.00 +0.00/-0.10	Diameter (mm):
<1	Centering (arcmin):
5.00 ±0.10	Center Thickness CT (mm):
	Edge Thickness ET (mm):

4.25	
	Clear Aperture CA (mm):
24	
	Bevel:
Protective as needed	
Optical Properties	
	Effective Focal Length EFL (mm):
200.00 @ 587.6nm	
	Back Focal Length BFL (mm):
198.35	
	Coating:
Uncoated	
	Substrate: ☐
N-K5	
	Surface Quality:
40-20	
	Power (P-V) @ 632.8nm:
1.5λ	
	Irregularity (P-V) @ 632.8nm:
λ/4	
	Focal Length Tolerance (%):
±1	
	f#:
8.00	
	Numerical Aperture NA:
0.06	
	Wavelength Range (nm):
330 - 2500	
Regulatory Compliance	
	Certificate of Conformance:
View	

Product Details

- N-K5 Substrate
 - Various Anti-Reflection (AR) Coatings
 - PCX and DCX Options Available
- N-K5 Lenses are available in various diameters, focal lengths, as well as Plano-Convex and Double-Convex form factors. Anti-reflective coatings covering the VIS to NIR make these ideal for multiple applications.

Technical Information



Compatible Mounts