

TECHSPEC[®] 25mm Dia. x 250mm FL, 3 - 12μm Coated, Ge Plano-Convex Lens



Stock **#87-951** 3-5 DAYS

[Other Coating Options](#)

-

1

+

S\$688.75

ADD TO CART

Qty 1-5

S\$688.75

Qty 6+

S\$551.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.1

Effective Focal Length EFL (mm):
250.00 @ 10.6μm

Back Focal Length BFL (mm):
249.25

Coating: BBAR (3000-12000nm)
Coating Specification: R _{avg} <5.0% @ 3 - 12µm
Substrate: ☐ Germanium (Ge)
Surface Quality: 60-40
Centering (arcmin): <3
Center Thickness CT (mm): 3.00 ±0.10
Edge Thickness ET (mm): 2.90
Radius R₁ (mm): 750.97
Clear Aperture CA (mm): 24
f/#: 10.00
Numerical Aperture NA: 0.05
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 3000 - 12000

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant