

TECHSPEC® 25mm Dia x -25mm FL Uncoated, Illumination Grade PCV Cylinder Lens



TECHSPEC® Illumination Grade PCV Cylinder Lenses

Stock **#46-196** 3-5 DAYS

⊖ 1 ⊕

S\$101.50

ADD TO CART

Qty 1-5

S\$101.50

Qty 6+

S\$81.20

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.2

Effective Focal Length EFL (mm):
-25.00

Substrate: ☐
[N-BK7](#)

f/#: 1.00
Numerical Aperture NA: 0.50
Coating: Uncoated
Type: Cylinder Lens, Plano-Concave
Wavelength Range (nm): 350 - 2200
Back Focal Length BFL (mm): -26.97
Center Thickness CT (mm): 3.00
Center Thickness Tolerance (mm): ±0.1
Edge Thickness ET (mm): 12.53
Focal Length Tolerance (%): ±3
Radius R₁ (mm): -12.96
Surface Quality: 60-40

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View