

TECHSPEC® 25mm Diameter x 20mm FL, Uncoated, K22R Plastic Aspheric Lens



TECHSPEC® Plastic Aspheric Lenses

Stock **#21-205** 3-5 DAYS

[Other Coating Options](#)



1



S\$71.05

ADD TO CART

Qty 1-24

S\$71.05

Qty 25+

S\$50.75

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
25.00 +/-0.15

Effective Focal Length EFL (mm):
20.00 @ 587.6nm

Numerical Aperture NA:
0.63

Back Focal Length BFL (mm): 14.38
Substrate:  Zeonex K22R
Aspheric Design Wavelength (nm): 587.6
Coating: Uncoated
Centering (arcmin): <5 (by design)
Surface Quality: 80-50
Clear Aperture CA (mm): 21.5
Edge Thickness ET (mm): 1.04
Center Thickness CT (mm): 9.29 ±0.20
f/#: 0.8
Bevel: Protective bevel as needed
Operating Temperature (°C): -30 to 70
Radius R₂ (mm): 103.1
Shape of Back Surface: Convex
Type: Aspheric Lens
Wavelength Range (nm): 350 - 1100
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View