

TECHSPEC® 25mm Diameter x 50mm FL Uncoated, UV PCX Cylinder Lens



Stock #68-172 CLEARANCE 3-5 DAYS

-

1

+

S\$159.43

ADD TO CART

Qty 1+

S\$159.43

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.2

Effective Focal Length EFL (mm):
50.00

Substrate: ☐
[Fused Silica](#) (Coming 7980)

f/#:
2.00

Numerical Aperture NA:
0.25

Coating:	Uncoated
Type:	Cylinder Lens, Plano-Convex
Wavelength Range (nm):	200 - 2200
Back Focal Length BFL (mm):	46.58
Center Thickness CT (mm):	5.00
Center Thickness Tolerance (mm):	±0.1
Edge Thickness ET (mm):	1.29
Focal Length Tolerance (%):	±3
Radius R (mm):	22.93
Surface Quality:	40-20
Wedge Tolerance (arcmin):	15.00

Regulatory Compliance

RoHS:	Compliant
Certificate of Conformance:	View